



Wafer Inspection System

OPTISTATION-3200/3100/3000



OPTISTATION-3200/3100



OPTISTATION-3000

Wafer Inspection System OPTISTATION-3200/3100

The OPTISTATION-3200/3100 is equipped with Nikon's acclaimed CFI₆₀-2 optics, producing clear images with high contrast and minimal flare.

Key Features

- Equipped with Nikon's proprietary CFI₆₀-2 optics to produce clear images with high contrast and minimal flare. The darkfield signal-to-background ratio is three times higher than with conventional Nikon optics, ensuring significantly better imaging.
- Nikon's acclaimed wide illuminator (WIL) and line illuminator (LIL) enable macro inspections under ideal conditions.
- State-of-the-art image processing and analysis technology enables highly accurate review inspections.
- Flexibility in load port positioning allows the OPTISTATION-3200/3100 to meet a variety of layouts and requirements of factory automation handling 300 mm wafers. OHT and other automatic transfer systems are supported too.
- Optimal recipe conditions are simply created by an easily accessible touch-screen. According to specifications of objective lens and wafer that is inspected, optimal observation settings, including aperture and light intensity can be set in advance.

Wafer Inspection System OPTISTATION-3000

The OPTISTATION is a wafer inspection system that enables simple and speedy manual visual inspection of 300 mm wafers. It contributes to dramatic increases in yields as an inline inspection system and analysis tool for R&D defect analysis.

Key Features

- The OPTISTATION-3000 inherits a system that boasts the high system stability and high-transfer rate, proven in front end process, of the OPTISTATION-3200/3100. The system provides the highest system reliability in its class, using a safety design that complies with SEMI standards.
- In addition to macro surface inspection, the system comes standard with edge inspection and the center of wafer back sides. The control of rotation speed and tilt angle during macro inspection can be manually adjusted from the default position using a joystick.
- Equipped with Nikon's proprietary CFI₆₀-2 optics to produce clear images with high contrast and minimal flare. The system comes standard with extra-long working distance lens and this suppresses image skipping when switching objectives from low to high magnification, enabling the system to deliver superior operatability and stability, combined with high resolution.
- Loading a 200 mm cassette adapter enables the combined transfer of 200-300 mm wafers on a single unit. There is no need for bothersome adjustments when making inch-size changes thanks to the load port's auto recognition of cassettes and the design of two-size shared parts. System uptime is thereby dramatically improved.

Specifications

- OPTISTATION-3200: 2 load port/300 mm wafer (200 mm wafer: option)
- OPTISTATION-3100: 1 load port/300 mm wafer (200 mm wafer: option)
- OPTISTATION-3000: 1 load port/300 mm wafer or 200 mm wafer



WARNING

TO ENSURE CORRECT USAGE, READ MANUALS CAREFULLY BEFORE USING YOUR EQUIPMENT.

The export of this product is controlled by Japanese Foreign Exchange and Foreign Trade Law and International export control regime. It shall not be exported without authorization from the appropriate governmental authorities.

Performance and equipment are subject to change without any notice or obligation on the part of the manufacturer. Products and brand names are trademarks or registered trademarks of their respective companies. February 2024
©2024 NIKON CORPORATION

<https://www.nikon.com/business/semi/>

Nikon Corporation Precision Equipment Group Marketing Department

Shinagawa Intercity Tower C, 2-15-3, Konan, Minato-ku, Tokyo 108-6290, Japan
Tel: +81-3-6433-3639

Nikon Precision Inc.

1399 Shoreway Road, Belmont, CA 94002-4107, U.S.A.
Tel: +1-(650)-508-4674

Nikon Precision Europe GmbH

Robert-Bosch-Strasse 11, D-63225 Langen, Germany
Tel: +49-6103-973-0

Nikon Instruments Korea Co., Ltd.

21F, City Air Tower, 36, Teheran-ro 87gil, Gangnam-gu, Seoul, 06164 Korea
Tel: +82-2-6288-1900

Nikon Precision Taiwan Ltd.

3F-1, NO.28, Taiyuan Street, Zhubei City, Hsinchu County 302, Taiwan, R.O.C.
Tel: +886-3-552-5888

Nikon Singapore Pte. Ltd.

18 Tai Seng Street #04-08, 18 Tai Seng, Singapore 539775
Tel: +65-6559-3618

Nikon Precision (Shanghai) Co., Ltd.

11-12F, Tower 5, Crystal Plaza No. 36, Ping Jia Qiao Road, Pudong New District, Shanghai 200126, China
Tel: +86-21-5899-0266

Nikon Precision Malaysia Sdn. Bhd.

No. 37-03-01, Ideal Golden Triangle, Jalan Dato' Ismail Hashim, 11900 Bayan Lepas, Penang, Malaysia
Tel: +60-4-371-7830